

По вопросам продаж и поддержки обращайтесь:

Архангельск +7 (8182) 45-71-35
Астрахань +7 (8512) 99-46-80
Астана +7 (7172) 69-68-15
Барнаул +7 (3852) 37-96-76
Белгород +7 (4722) 20-58-80
Брянск +7 (4832) 32-17-25
Владивосток +7 (4232) 49-26-85
Владимир +7 (4922) 49-51-33
Волгоград +7 (8442) 45-94-42
Воронеж +7 (4732) 12-26-70
Екатеринбург +7 (343) 302-14-75
Иваново +7 (4932) 70-02-95
Иркутск +7 (3952) 56-24-09
Иошкар-Ола +7 (8362) 38-66-61
Ижевск +7 (3412) 20-90-75
Казань +7 (843) 207-19-05

Курск +7 (4712) 23-80-45
Липецк +7 (4742) 20-01-75
Магнитогорск +7 (3519) 51-02-81
Москва +7 (499) 404-24-72
Мурманск +7 (8152) 65-52-70
Набережные Челны +7 (8552) 91-01-32
Нижний Новгород +7 (831) 200-34-65
Нижевартонск +7 (3466) 48-22-23
Нижнекамск +7 (8555) 24-47-85
Новосибирск +7 (383) 235-95-48
Калуга +7 (4842) 33-35-03
Калининград +7 (4012) 72-21-36
Кемерово +7 (3842) 21-56-70
Киров +7 (8332) 20-58-70
Краснодар +7 (861) 238-86-59
Новороссийск +7 (8617) 30-82-64

Омск +7 (381) 299-16-70
Орел +7 (4862) 22-23-86
Оренбург +7 (3532) 48-64-35
Пенза +7 (8412) 23-52-98
Пермь +7 (342) 233-81-65
Первоуральск +7 (3439) 26-01-18
Ростов-на-Дону +7 (863) 309-14-65
Рязань +7 (4912) 77-61-95
Самара +7 (846) 219-28-25
Санкт-Петербург +7 (812) 660-57-09
Саратов +7 (845) 239-86-35
Саранск +7 (8342) 22-95-16
Сочи +7 (862) 279-22-65
Ставрополь +7 (8652) 57-76-63
Сургут +7 (3462) 77-96-35
Смоленск +7 (4812) 51-55-32

Сызрань +7 (8464) 33-50-64
Сыктывкар +7 (8212) 28-83-02
Тверь +7 (4822) 39-50-56
Томск +7 (3822) 48-95-05
Тула +7 (4872) 44-05-30
Тюмень +7 (3452) 56-94-75
Ульяновск +7 (8422) 42-51-95
Уфа +7 (347) 258-82-65
Хабаровск +7 (421) 292-95-69
Челябинск +7 (351) 277-89-65
Чебоксары +7 (8352) 28-50-89
Череповец +7 (8202) 49-07-18
Ярославль +7 (4852) 67-02-35

сайт: promag.pro-solution.ru | эл. почта: ehr@pro-solution.ru

телефон: **8-800-511-8870**

Россия, Казахстан и другие страны ТС доставка в любой город

Анализатор Handheld for digital sensors Liquiline To Go CYM291



With Liquiline To Go CYM291 you get the information you need, where you need it. The robust multiparameter handheld enables you to control any measuring point – even in hazardous areas – with the identical Memosens sensors that you use in your process. This guarantees full data consistency between your measurements with results you can trust: reliable measuring values that allow you to quickly take any remedial actions necessary to keep your process running under optimal conditions.

Принцип измерения

Стеклянный электрод

Применение

для полевого и лабораторного применения

Принцип измерения

pH, проводимость и растворенный кислород –датчики с технологией Memosens

Конструкция

Портативный прибор

Габаритные размеры

прибл. (132x156x30) мм

(5,2x6,14x1,18) дюйма

Сертификаты на взрывозащиту

IECEx: Ex ia IIC T4/T3 Ga

ATEX II 1 G Ex ia IIC T4/t3 Ga

Степень защиты

IP 66/67

Входной сигнал

Контакт M8 для протокола слаботочной связи Memosens. Одноканальный прибор

Дополнительные сертификаты

Электромагнитная совместимость

Характеристики

Бренд: Promag